

ESTRATTORI PER VALVOLE

EW3900

Estrattore per valvola

Un sistema semplice ed efficace che permette la rimozione e la sostituzione di meccanismi di carica senza disperdere un grammo di refrigerante.

Permette inoltre la ricarica molto più veloce del sistema A/C, togliendo il meccanismo di carica e reinserendolo una volta terminata la carica stessa.




Codice	Modello
08008023002	EW 3900
08008023003	EW 3900/5

Attacco femmina girevole	Attacchi maschio	Dimensioni	Peso
1/4" SAE	1/4" SAE	100 x 175 x 30 mm	0,10 kg
5/16" SAE	1/4" SAE	100 x 175 x 30 mm	0,10 kg



Schema di funzionamento: come sostituire o rimuovere il meccanismo di carica senza disperdere refrigerante



EW4900

Estrattore per valvola con duplice attacco di servizio

L'EW4900 consente di rimuovere il meccanismo interno della valvola di servizio, e quindi aprire la via alle sue due connessioni SAE M integrate da 3/8" e 1/4" dotate di rispettiva valvola.

L'attacco da 3/8" SAE M risulta ottimale per l'accoppiamento con il Tubo IperVAC (vedi pag 42) al fine di ridurre notevolmente i tempi necessari per effettuare un efficace vuoto. La seconda porta da 1/4" SAE M è ideale per connettere vacuometro digitale, tubo di carica o gruppo manometrico.




Codice	Modello	Descrizione
08008060002	EW 4900	Estrattore 1/4" con duplice valvola e connessione
08008060003	EW 4900/5	Estrattore 5/16" con duplice valvola e connessione

Attacco femmina girevole	Attacchi maschio	Dimensioni	Peso
1/4" SAE	3/8" SAE + 1/4" SAE	100 x 175 x 30 mm	0,25 kg
5/16" SAE	3/8" SAE + 1/4" SAE	100 x 175 x 30 mm	0,25 kg



Esempio applicativo:



Accessori e ricambi

Codice	Modello	Descrizione
06140002	IVSS/6-6/60	Tubo IperVAC 1500mm con connessione 3/8" SAE
06140001	IVSS/6-6/36	Tubo IperVAC 900mm con connessione 3/8" SAE
14020097	G-LV/T-WIG	Kit 5pz guarnizioni per EW3900/4900
08008059	LOCK VALVE CARE	Utensile per semplice sostituzione guarnizioni in Lock Valve, EW e tubi flessibili
05108043001	M1/4"-R134A/V-RK	Kit 10 pz meccanismi interni per HFC (R134a-R410A, R32...)
05055099	W404/5	Adattatore 1/4" SAE F x 5/16" SAE M

CORE SCREWER TOOL



EW3900

Core screwer tool

Easy and efficient system that enables to remove and replace valve cores without dispersing one gramme of refrigerant. It also enables to recharge the A/C system faster by removing the valve core and reinserting it again once charging is over.



Code	Model
08008023002	EW 3900
08008023003	EW 3900/5

Swivel female connections	Male connections	Dimensions	Weight
1/4" SAE	1/4" SAE	100 x 175 x 30 mm	0,10 kg
5/16" SAE	1/4" SAE	100 x 175 x 30 mm	0,10 kg



Functioning diagrams: how to remove and replace valve cores without dispersing one gramme of refrigerant.



A



B



C

EW4900

Core removal access solution with dual connections

EW4900 enables to remove the valve core, and then open the way to its two integrated SAE M 3/8" and 1/4" connections equipped with valves.

3/8" port designed for coupling with the IperVAC hose (see pag 32) and 1/4" port for vacuum digital gauge, charging hose or manifold.




Code	Model	Description
08008060002	EW 4900	1/4" core removal solution with double connections
08008060003	EW 4900/5	5/16" core removal solution with double connections

Swivel female connections	Male connections	Dimensions	Weight
1/4" SAE	3/8" SAE + 1/4" SAE	100 x 175 x 30 mm	0,25 kg
5/16" SAE	3/8" SAE + 1/4" SAE	100 x 175 x 30 mm	0,25 kg




Application:



Mechanism Removal

A



Vacuum

Vacuum pump

B



Charge

C



Accessories and Spare parts

Code	Model	Description
06140002	IVSS/6-6/60	IPERVAC 1500 mm hose 3/8" connection
06140001	IVSS/6-6/36	IPERVAC 900 mm hose 3/8" connection
14020097	G-LV/T-WIG	Kit 5 pcs gaskets for LOCK-VALVE - EW3900/EW4900
08008059	LOCK VALVE CARE	Gasket replacement tool for LOCK-VALVE, EW and hoses
05108043001	M1/4"-R134A/V-RK	Kit 10 pcs internal cores for HFC (R134a-R410A, R32,...)
05055099	W404/5	1/4" SAE F x 5/16" SAE M adapter